

PLUGSTATION®

EARPLUG DISPENSER, CORDED



*Pull to dispense
corded earplugs*

KEEP AN EARFUL WITHIN EASY REACH

Moldex now offers the convenience, increased compliance and cost savings of the PlugStation to those that require a corded earplug. With the PlugStation, you can afford to put earplugs in all the places they're needed. Hang one near workstations, outside the restrooms, and in the breakroom. Easy convenient access to hearing protection will ensure that the earplugs are being used and will save time.

INCREASED COMPLIANCE AND COST SAVINGS

Convenient, quick access and ease of use lead to higher compliance. Plus, because workers take one pair at a time, there is less waste. Less waste means more cost savings.

HYGIENIC FROM DISPENSER TO YOUR HAND

With new Corded PlugStations, you pull to dispense corded earplugs right to your hand, so you don't have to worry about plugs falling on the floor or trays collecting dust and contaminants. When the PlugStation is empty simply toss it and hang a new one - no fumbling with messy, hard to use refills.

NOW AVAILABLE WITH GLIDE® FOAM TWIST-IN EARPLUGS WITH CORD

Our highly popular Glide Foam Twist In earplug with Cord is now available in the PlugStation dispenser. Glide Foam has the highest independently rated NRR (30) for a no-roll earplug.

FEATURES

- Gives workers easy access to hearing protection.
- 150 pairs in each PlugStation.
- Compliance – High visibility to increase awareness for your hearing conservation program.
- Convenience – Hang a PlugStation® anywhere plugs are needed.
- Cost Savings – Workers take one pair at a time so there are no wasteful grabbing of multiple pairs.
- All Moldex hearing protection is independently tested to ANSI S3.19-1974.
- 100% PVC-Free.

AVAILABLE EARPLUGS, 150PR/PLUGSTATION



6880
SparkPlugs®
PlugStation, Corded
NRR 33dB



6881
SparkPlugs®
PlugStation, Corded
Metal Detectable
NRR 33dB



6882
Pura-Fit®
PlugStation, Corded
NRR 33dB



6883
Glide® Foam w/ Cord
PlugStation
NRR 30dB

PLUGSTATION®

EARPLUG DISPENSER, CORDED

PART # / DESCRIPTION	DISPLAY	CASE
6880 SparkPlugs	150 Pairs	4 Dispensers
6881 Metal Detectable SparkPlugs	150 Pairs	4 Dispensers
6882 Pura-Fit	150 Pairs	4 Dispensers
6883 Glide Foam	150 Pairs	4 Dispensers

WARNING TO USER

1. Use these laboratory derived attenuation data for comparison purposes only. The amount of protection afforded in field use often is significantly lower depending upon how the protectors are fitted and worn.
2. Failure to obtain a proper fit will reduce effectiveness of hearing protectors and could result in hearing loss or injury.
3. Over protection can be dangerous. The wearer must be able to hear warning signals.
4. Wearers with hearing loss should exercise extreme caution.
5. It is the employer's responsibility to ensure that the type of hearing protector and its rating is appropriate for the user in their particular workplace.
6. Failure to follow all instructions and warnings could result in increased risk of hearing loss, serious injury or death.
7. Use caution when working around machinery or any other equipment to ensure neck cord does not become caught or entangled.
8. Moldex foam earplugs must only be used as part of a hearing conservation program that complies with applicable local safety and health regulations.

MOLDEX TECHNICAL ASSISTANCE

Moldex provides all of the technical assistance required to set up a hearing protection program. For more information call +1 (800) 421-0668 or +1 (310) 837-6500 ext. 512/550 or E-mail: tech@moldex.com or visit www.moldex.com.

Keep earplugs away from infants and small children as they may get caught in the windpipe and create a choking hazard.



DISTRIBUTED BY:

MOLDEX®
Ideas that wear well.®

MOLDEX-METRIC, INC.
10111 Jefferson Blvd.
Culver City, CA 90232
TEL: +1 (800) 421-0668 or
+1 (310) 837-6500
FAX: +1 (310) 837-9563
E-mail: sales@moldex.com
www.moldex.com

CANADIAN CUSTOMER SERVICE
Tel: +1 (800) 421-0668, Ext. 550/510
Fax: +1 (310) 837-9563

ATTENUATION DATA OF PURA-FIT®

Tested According to ANSI Specs S3.19-1974 Michael & Assoc., State College, PA

Frequency (Hz)	125	250	500	1000	2000	3150	4000	6300	8000		
Mean Attenuation (dB)	42.4	43.5	45.9	39.8	36.8	44.5	46.6	48.1	47.4	NRR 33	CSA AL
Standard Deviation (dB)	4.9	4.2	4.9	3.4	2.0	3.7	2.9	4.6	4.7		

ATTENUATION DATA OF SPARKPLUGS® AND METAL DETECTABLE SPARKPLUGS®

Tested According to ANSI Specs S3.19-1974 Michael & Assoc., State College, PA

Frequency (Hz)	125	250	500	1000	2000	3150	4000	6300	8000		
Mean Attenuation (dB)	42.3	43.7	46.6	40.9	38.6	44.7	46.9	49.3	48.3	NRR 33	CSA AL
Standard Deviation (dB)	5.0	6.0	5.8	4.2	2.8	3.2	3.3	4.2	3.6		

ATTENUATION DATA OF GLIDE® FOAM

Tested According to ANSI Specs S3.19-1974 Michael & Assoc., State College, PA

Frequency (Hz)	125	250	500	1000	2000	3150	4000	6300	8000		
Mean Attenuation (dB)	31.7	32.2	36.1	37.8	40.9	42.7	41.2	46.2	48.0	NRR 30	CSA AL
Standard Deviation (dB)	5.2	3.5	4.4	3.3	3.2	2.2	3.0	4.1	4.3		



Printed on Recycled Paper