



METAL DETECTABLE HEARING PROTECTION

Disposable Foam And Reusable Earplugs For Food Processing


MAXIMIZE FOOD SAFETY IN YOUR PROCESSING PLANT

Detection of contaminants is a key part of food safety. Moldex has both disposable and reusable metal detectable hearing protection that has been carefully crafted for safety.

INDEPENDENTLY DETECTABLE

SparkPlugs® and Rockets® metal detectable hearing products feature both a metal detectable cord and a metal detectable earplug for maximum safety.

The Alphas® have a braided cord which is NOT metal detectable. The earplug is metal detectable. The enclosed metal ball bearing eliminates any exposed metal on the plug. The ball bearing and the cord are in separate holes so that the earplugs remain metal detectable even if the cord is removed.



- ✓ The SparkPlugs® and Rockets® plug and cord are independently detectable for added safety (the Alphas® cord is not detectable).
- ✓ Corded and bright blue specifically for food processing.
- ✓ Comfort and ease of use for higher compliance.
- ✓ Convenience, high visibility, and ease of use of PlugStation helps support greater compliance and cost savings.
- ✓ All Moldex hearing protection is independently tested to ANSI S3.19-1974 for protection you can count on.
- ✓ All Moldex products and packaging are 100% PVC free.

MODEL NUMBER	DESCRIPTION	DISPLAY QUANTITY	CASE QUANTITY
6415	Rockets® Metal Detectable Corded	50 Pairs	4 Boxes
6436	Alphas® Metal Detectable Corded	50 Pairs	4 Boxes
6615	SparkPlugs® Metal Detectable Corded	100 Pairs	20 Boxes
6881	SparkPlugs® Metal Detectable PlugStation	150 Pairs	4 Dispensers

Always refer to warnings and instructions prior to use.

MOLDEX®

METAL DETECTABLE HEARING PROTECTION

CORDED AND BLUE FOR ADDED SAFETY

Our disposable Metal Detectable SparkPlugs earplugs and our reusable Metal Detectable Rockets and Alphas are corded to help prevent plug loss. The bright blue color is ideal for food processing applications.

SPARKPLUGS AVAILABLE IN PLUGSTATION® DISPENSER

Moldex offers the convenience, increased compliance and cost savings of our popular earplug dispenser, the PlugStation®, with Metal Detectable SparkPlugs. With the PlugStation you can afford to put earplugs in all the places they're needed. Convenience, ease of use, and high visibility lead to higher compliance and by giving quick access to workers it also saves worktime. Workers take one pair at a time so there are no wasteful grabbing of multiple pairs and cost savings are increased.

SOFT COMFORTABLE FIT

SparkPlugs earplugs are made of extra-soft, extra-light foam and have a non-irritating smooth surface. Their tapered shape fits easily in the ear canal, and seals gently and snugly without pressure. They're so comfortable you'll forget you're wearing earplugs.

Rockets have an air bubble in the tip to provide cushioned comfort for all-day wear. The soft, flexible flanges provide a superior seal and fit most size ear canals. The easy grip handle lets them easily slip into the ear and Rockets can be washed and reused.

Alphas offer a premium product at an economical price thanks to innovative engineering.

ATTENUATION DATA / DATOS DE ATENUACIÓN / DONNÉES D'ATTÉNUATION FOR 6615

Tested According to ANSI Specs S3.19-1974 by Michael & Assoc., State College, PA.

Probado de acuerdo a las especificaciones ANSI S3.19-1974 Michael & Assoc., State College, PA.

Tests Conformes aux Spéc. ANSI S3.19-1974 Michael & Assoc., State College, PA.

Frequency (Hz) Frecuencia (Hz) Fréquence	125	250	500	1000	2000	3150	4000	6300	8000		
Mean Attenuation (dB) Atenuación de Dato (dB) Atténuation Moyenne (dB)	42.3	43.7	46.6	40.9	38.6	44.7	46.9	49.3	48.3	NRR 33	CSA AL
Standard Deviation (dB) Desviación Standard (dB) Ecart Standard (dB)	5.0	6.0	5.8	4.2	2.8	3.2	3.3	4.2	3.6		

ATTENUATION DATA / DATOS DE ATENUACIÓN / DONNÉES D'ATTÉNUATION FOR 6415

Tested According to ANSI Specs S3.19-1974 by Michael & Assoc., State College, PA.

Probado de acuerdo a las especificaciones ANSI S3.19-1974 Michael & Assoc., State College, PA.

Tests Conformes aux Spéc. ANSI S3.19-1974 Michael & Assoc., State College, PA.

Frequency (Hz) Frecuencia (Hz) Fréquence	125	250	500	1000	2000	3150	4000	6300	8000		
Mean Attenuation (dB) Atenuación de Dato (dB) Atténuation Moyenne (dB)	34.3	35.3	36.8	34.7	35.5	40.5	37.5	40.3	44.4	NRR 27	CSA AL
Standard Deviation (dB) Desviación Standard (dB) Ecart Standard (dB)	4.1	4.4	5.1	3.1	3.4	3.7	3.8	6.2	3.8		

ATTENUATION DATA / DATOS DE ATENUACIÓN / DONNÉES D'ATTÉNUATION FOR 6436

Tested According to ANSI Specs S3.19-1974 by Michael & Assoc., State College, PA.

Probado de acuerdo a las especificaciones ANSI S3.19-1974 Michael & Assoc., State College, PA.

Tests Conformes aux Spéc. ANSI S3.19-1974 Michael & Assoc., State College, PA.

Frequency (Hz) Frecuencia (Hz) Fréquence	125	250	500	1000	2000	3150	4000	6300	8000		
Mean Attenuation (dB) Atenuación de Dato (dB) Atténuation Moyenne (dB)	36.0	33.7	37.3	37.2	37.7	39.8	37.8	37.8	43.5	NRR 27	CSA AL
Standard Deviation (dB) Desviación Standard (dB) Ecart Standard (dB)	4.6	4.7	5.0	5.0	3.8	3.2	3.3	4.1	5.1		

WARNINGS

1. Use these laboratory derived attenuation data for comparison purposes only. The amount of protection afforded in field use often is significantly lower depending upon how the protectors are fitted and worn.
2. Failure to follow all instructions and warnings could result in increased risk of hearing loss, serious injury or death.
3. Failure to obtain a proper fit will reduce effectiveness of hearing protectors and could result in hearing loss or injury.
4. Over protection can be dangerous. The wearer must be able to hear warning signals.
5. Wearers with hearing loss should exercise extreme caution.
6. It is the employer's responsibility to ensure that the type of hearing protector and its rating is appropriate for the user in their particular workplace.
7. Earplugs must only be used as part of a hearing conservation program that complies with applicable local safety and health regulations.
8. If irritation, redness or discomfort occurs, discontinue use and consult a licensed health practitioner.
9. If earplug is corded, use caution when working around machinery or any other equipment to ensure neck cord does not become caught or entangled.



Keep earplugs away from infants and children as they may get caught in the windpipe and create a choking hazard. If corded, the cord is a potential strangulation hazard.

Always refer to warnings and instructions prior to use. 100% PVC-Free for a more sustainable alternative.

MOLDEX TECHNICAL ASSISTANCE

Moldex provides all of the technical assistance required to set up a hearing protection program. For more information call +1 (800) 421-0668 or +1 (310) 837-6500 ext. 512, or email: tech@moldex.com or visit www.moldex.com.

MOLDEX-METRIC, INC.

10111 Jefferson Blvd., Culver City, CA 90232
TEL: +1 (800) 421-0668 or +1 (310) 837-6500
EMAIL: sales@moldex.com
www.moldex.com

U.S. & CANADA CUSTOMER SERVICE

TEL: +1 (800) 421-0668, Ext. 550

For user instructions refer to packaging or visit
<https://www.moldex.com/resources/instructional-resources/fitting-instructions-hearing/>



Made in USA
Hecho en USA
Fabriqué aux É.U.



PVC FREE
Libre de PVC
PVC Gratuit

Moldex®, PlugStation®, SparkPlugs®, Rockets®, Alphas®, the PVC-Free® logo and random colored streaks and swirls are registered trademarks of Moldex-Metric, Inc.
U.S. Patents #8,671,948, D721,960, #12,082,993 and #D1,044,317.

MKT-1018 REV B 4/25